
# 617 Electrometer/Source



For most new applications our Model 6517A (page A-69) offers better performance than the 617 at a similar cost. The 617-HIQ, however, offers the highest charge measuring capability of any of our instruments.

The 617 can measure resistances or generate I-V curves using either of two measurement techniques. Using the InA to 100µA decade current source, a known constant current is forced through the unknown resistance. The developed voltage is measured with a high input impedance voltmeter, and the resistance or voltage is displayed and transmitted over the IEEE-488 bus. Alternately, the 617's programmable voltage source is applied across the unknown resistance and the resulting current is detected by the 617's sensitive current circuitry. Current may be displayed directly, or resistances as high as  $10^{16}\Omega$  can be directly measured; the 617 can calculate and display the quantity V/I.

# ORDERING INFORMATION

617 Hectrometer/Source with Model 6011 Input Leads and Model 6172 Triax Adapter

617-HIQ Electrometer/Source with extended charge measurement range, Model 6011 Input Leads and Model 6172 Triax Adapter

This product is available with an Extended Warranty. See section C for complete ordering information.

The 617's built-in IEEE-488 interface makes all controls programmable.

Pushbutton suppression lets you make relative measurements with respect to a selected baseline, or cancel background signals. ZERO CORRECT cancels internal offsets at the touch of a button. Both are bus programmable.

The built-in V- $\Omega$  GUARD switch lets you drive the inner shield of the triaxial input cable at guard voltage, minimizing leakage current and time constants. 100-point data storage is also built in, with

Min/Max readings available from front panel or bus.

For measurements of charge as high as 20µC, the 617-HIQ version offers three higher charge ranges. These higher ranges have proven useful on Faraday cup measurements and other static charge applications including photo-

copy research and development.



16, rue Sadi Carnot - Z.A "La Pépinière" 94880 NOISEAU

Tél.: 01 45 90 99 22 - Fax: 01 45 90 99 66

- Built-in V source
- Full autoranging
- Built-in IEEE-488 interface
- Built-in V-Ω Guard
- Resistance measurement from 0.1 $\Omega$  to >1016 $\Omega$

### ACCESSORIES AVAILABLE

#### PROBE

6103C Voltage Divider Probe (1000:1) (requires 6012 adapter)

#### CABLES

6011 Input Leads, triax to clips, 1.5m (5 ft)

6011-10 Input Leads, triax to clips, 3m (10 ft)

7024-3 Triaxial Cable, 0.9m (3 ft)

7024-10 Triaxial Cable, 3m (10 ft)

### ADAPTERS

6012 Triaxial to Coaxial UHF Adapter

6146 Triax Tee Adapter

6147 Male Triax to Female BNC Adapter

6171 3-Slot Male to 2-Lug Female Triaxial Adapter

6172 2-Slot Male to 3-Lug Female Triaxial
Adapter

7023 Female Triaxial Bulkhead Connector

#### TEST FIXTURES

6105 Resistivity Chamber

8002A Guarded High Resistance Test Fixture

# RACK MOUNT KITS

1019A-1 Single Fixed Rack Mount Kit


1019A-2 Dual Fixed Rack Mount Kit

1019S-1 Single Slide Rack Mount Kit

1019S-2 Dual Slide Rack Mount Kit

4288-4 Dual Fixed Rack Mount Kit

See page A-231 for descriptions of all accessories.



# 617 Electrometer/Source

Tests et Mesures Electroniques

16, rue Sadi Carnot - Z.A "La Pépinière" 94880 NOISEAU

VOLTS RANGE	RESO- LUTION	ACCURACY (1 Year)* 18°–28°C ±(%rdg+counts)	TEMPERATURE COEFFICIENT 0°-18°C & 28°-50°C ±(%rdg+counts)/°C
200 mV	10 μV	0.05 + 4	0.004 + 3
44 24 V	- \$-100 μV	0.05 4 1	0.004 £0.3
20 V	l mV	0.05 + 1	0.005 + 0.1
200 V	10 mV	0.07 +1	0.007 + 0.1

\*When properly zeroed.

NMRR: >80dB on 200mV, 60dB on 2V and 20V, 55dB on 200V range, at 50Hz or 60Hz ±0.1%.

CMRR: >120dB at DC, 50Hz or 60Hz.

INPUT IMPEDANCE: >200T $\Omega$  in parallel with 20pF (<2pF guarded).

GAIN ERROR AT PREAMP OUTPUT: Typically 5ppm.

SMALL SIGNAL BANDWIDTH AT PREAMP OUTPUT: Typically 100kHz (-3dB).

AMPS		ACCURACY (1 Year)*	TEMPERATURE COEFFICIENT 0°-18°C & 28°-50°C ±(%rdg+counts)/°C	
RANGE	RESO- LUTION	18°-28°C ±(%rdg+counts)		
2 pA	100 aA	1.6 + 66	0.15 + 8	
20 pA	1 fA	1.6 + 7	0.15 + 1	
200 pA	10 fA	1.6 + 1	0.15 + 0.1	
. 2 nA	100 fA	.e 0.25.+ 5	0.015 ± 3	
20 nA	l pA	0.25 + 1	0.015 + 0.3	
200 nA	10 pA	0.25 + 1	0.015.4 0.1	
2 μΑ	100 pA	0.15 + 4	0.005 + 3	
20 µA 💠	1 nA	0.15 +1-1	0.005 + 0.3	
200 μΑ	IO nA	0.15 + 1	0.006 + 0.1	
2 mA	100 nA 🔆	0.15 + 4	0.005 + 3	
20 mA	lμA	0.15 + 1	0.005 + 0.3	

<sup>\*</sup>When properly zeroed using recommended warm-up procedure.

INPUT BIAS CURRENT: <5fA at 23°C

INPUT VOLTAGE BURDEN: <1mV except 3mV on 20mA range.

PREAMP SETTLING TIME (to 10% of final value): 2.5s on pA, 15ms on nA, 5ms on µA and mA ranges.

NMRR: >95dB on pA, 60dB on nA,  $\mu$ A, and mA ranges at 50Hz or 60Hz  $\pm$ 0.1%.

And the second of the second	and the second second	The second second second	
COULOMB	S		TEMPERATURE
(617)		ACCURACY	COEFFICIENT
		(1 Year)*	0°-18°C &
	RESO-	18°-28°C	28°-50°C
RANGE	LUTION	±(%rdg+counts)	±(%rdg+counts)/°C
200 pC	10 fC	0.4 + 4	0.02 + 3
2 nC	100 fC	0.4 + 1	0.02 + 0.3
20 nC	1 pC	0.4+1 .	0.02 + 0.1
(617-HIQ)			
200 nC	10 pC	2.0 + 4	0.04 + 3
- 2 μC	100 pC	2.0+1	0.04+0.3
20 μC	1 nC	2.0 + 1	0.04 + 0.1

<sup>\*</sup>When properly zeroed.

INPUT BIAS CURRENT: <5fA at 23°C.

## **IEEE-488 BUS IMPLEMENTATION**

MULTILINE COMMANDS: DCL, LLO, SDC, GET, GTI, UNT, UNI, SPE, SPD. UNILINE COMMANDS: IFC, REN, EOI, SRQ, ATN.

INTERFACE FUNCTIONS: SH1, AH1, T5, TE0, L4, LE0, SR1, RL0, PP0, DC1, DT1, C0, E1.

PROGRAMMABLE PARAMETERS: Function, Range, Zero Check, Zero Correct, Zero Suppress, EOI, Trigger, Terminator, 100-Reading Storage and Retrieval, Calibration, V Source Output, Display Format, SRQ, Status (including V Source I-Limit), Output Format.

ADDRESS MODES: TALK ONLY and ADDRESSABLE.

TRIGGER TO READING DONE: 350ms typical.

OHMS	or the control of the	ACCURACY*	5 90 99 22 - Fax : 01 TEMPERATURE	45 90 99 66
RANGE	RESO- LUTION	(1 Year) 18°–28°C ±(%rdg+counts)	COEFFICIENT 0°-18°C & 28°-50°C ±(%rdg+counts)/°C	TEST CURRENT ±1.5%
2 kΩ	100 mΩ	0.20 + 4	0.01 + 3	100 μΑ
20 kΩ	$1 \leq \Omega + \cdots$	0.15 # 11 # 44	0.01 4 0.3	100 uA
200 kΩ	10 Ω	0.25 + 1	0.01 + 0.3	10 μΑ
2 MΩ	- 100 J-Ω (100	- 10,25 ± 15 cm	0.02 + 0.3	LUA
20 MΩ	1 kΩ	0.25 + 1	0.02 + 0.3	100 nA
200 MΩ	🦈 10 ο kΩ 🤄	0.30 1 1 4	0.02+0.3	10 nA 🔻
2 GΩ	100 kΩ	1.5 + 1	0.04 + 0.3	l nA
20 GΩ	. · · · <u>1</u> ΜΩ , · · ·	15 4 1 No.	0.04 + 0.1	ThAV
200 GΩ	10 MΩ	1.5 + 1	0.04 + 0.1	l nA

<sup>\*</sup>When properly zeroed.

MAXIMUM OPEN CIRCUIT VOLTAGE: 300V DC.

PREAMP SETTLING TIME (To 0.1% of final reading with <100pF input capacitance):  $2k\Omega$  through  $20M\Omega$ : 15ms;  $200M\Omega$ : 15ms;  $200M\Omega$ : 15ms;  $200M\Omega$ : 15ms;  $20G\Omega$ : 10ms;  $20M\Omega$ : 10ms; 10ms

V/I MODE: Used with V source; displays resistance  $(5 \times 10^4 \text{ to } 10^{15}\Omega)$  calculated from measured current. V/I Ohms accuracy equal to accuracy of V source plus accuracy of selected amps range.

#### VOLTAGE SOURCE

OUTPUT: -102V to +102V in 50mV steps.

ACCURACY (1 Yr., 18°-28°C): ±(0.2% + 50mV).

TEMPERATURE COEFFICIENT: ±(0.005% + 1mV)/°C

 $\textbf{MAXIMUM OUTPUT CURRENT: $\pm 2\text{mA; active current limit at $< 4\text{mA}$ with annunciation.}$ 

SETTLING TIME: <3ms to rated accuracy.

NOISE: <(1ppm of output voltage + 200µV) p-p from 0.1Hz to 10Hz.

#### GENERAL

DISPLAY: 4½-digit numeric LEDs with appropriate decimal point and polarity indication; signed two-digit alphanumeric exponent.

OVERRANGE INDICATION: Display reads "OL".

RANGING: Automatic or manual.

CONVERSION TIME: 330ms.

DATA STORE and MIN/MAX: 100-reading store capacity; records data at one of six selectable rates from every reading to 1 reading/hour, or by manual triggering. Also detects and stores maximum and minimum readings continuously while in the Data Store mode.

PROGRAMS: Provide front panel access to IEEE address, choice of engineering units or scientific notation, and digital calibration.

MAXIMUM INPUT: 250V peak, DC to 60Hz sine wave; 10s per minute maximum on mA ranges.

MAXIMUM COMMON MODE VOLTAGE (DC to 60Hz sine wave): Electrometer, 500V peak; V
Source, 100V peak.

ISOLATION (Input LO to chassis): Typically  $10^{10}\Omega$  in parallel with 500 pE

INPUT CONNECTOR: Two lug triaxial on rear panel.

OUTPUT CONNECTORS: 5-way binding posts on rear panel for V source, preamp, and analog outputs. Rear panel BNC for External Trigger and Meter Complete.

2V ANALOG OUTPUT: 2V for full range input. Inverting in Volts and Ohms modes. Output impedance  $10k\Omega.$ 

PREAMP OUTPUT: Provides a guard output for Volts and Ohms measurements. Can be used as an inverting output or with external feedback in Amps and Coulombs modes. Output impedance  $100\Omega$ .

GAIN ERROR AT PREAMP OUTPUT: Typically 5ppm.

SMALL SIGNAL BANDWIDTH AT PREAMP OUTPUT: Typically  $-3 \, \mathrm{dB}$  at  $100 \mathrm{kHz}$ .

EXTERNAL TRIGGER: TTL compatible External Trigger and Electrometer Complete.

V, Ω GUARD SWITCH: OFF position: Inner shield of triax is Input LO, input capacitance is ≤20pE ON position: Inner shield of triax is Guard (follows input HI). Input capacitance is ≤2pE. Use Analog Output COM for Input LO connection.

ENVIRONMENT: Operating: 0°-50°C; relative humidity 70% non-condensing, up to 35°C. Storage: -25° to +65°C.

SHIELDING: Double shielded.

weight 3.6kg (8 lb).

WARM-UP: 2 hours to rated accuracy (see manual for recommended procedure).

POWER: 105–125V or 210–250V (internal switch selected), 90–110V available; 50–60Hz, 25VA. DIMENSIONS, WEIGHT: 127mm high  $\times$  216mm wide  $\times$  359mm deep (5 in  $\times$  8½ in  $\times$  14½ in). Net

ACCESSORIES SUPPLIED: Model 6011 Input Leads and Model 6172 Triax Adapter.

A-64

**KEITHLEY** 

SENSITIVE MEASUREMENTS